



Offering you the latest  
innovative products & solutions  
from **Siemens**

## Need a quote?

YOU WILL GET **EXTRA SAVING** EVERY TIME WITH OUR QUOTATION SERVICE.

There is no need for you to spend time visiting lots of supplier's sites to find the best price for each product. Just give us the manufacturer's part number. We will check it for you and make sure you pay the lowest price possible.

Contact our dedicated Quotation Team with your latest order, and our team will work out where we can find savings for you.



1300 656 636  
quotesandtenders@rs-components.com  
au.rs-online.com

Join the conversations



Terms & Conditions

To view our latest prices, charges and full terms see RS Conditions of Sale as set out online at [au.rs-online.com](http://au.rs-online.com). Prices correct at the time of going to print, prices exclude GST. Published by: RS Components Pty Ltd, 25 Pavese Street Smithfield NSW 2164

RS Components Pty Ltd July 2017.  
RS are trademarks of RS Components Limited.  
An Electrocomponents Company.

# SIEMENS

Siemens is a global powerhouse focusing on the areas of electrification, automation and digitalization. One of the world's largest producers of energy-efficient, resource-saving technologies, Siemens is a leading supplier of systems for power generation and transmission as well as medical diagnosis.

With over 5,500 innovative products and solutions from Siemens available at RS Online, backed by our reliable world class delivery - we enable our customers to set industry benchmarks.

Make RS your first choice for Siemens, visit [au.rs-online.com](http://au.rs-online.com) today



### Save time with one-stop buying

Take advantage of our vast range to make us the one-stop supplier for all the parts you want, at competitive prices



### Availability and breadth of range

We can provide all the necessary components with great prices and fast delivery.



### Additional Support

We're here and happy to help!  
You can contact our friendly customer service team on **1300 656 636** or [ozorder@rs-components.com](mailto:ozorder@rs-components.com)



visit [au.rs-online.com](http://au.rs-online.com)



## Easy Steps to a user-defined website

Interconnected components and access to devices via the Web are the new trend: Switch on the heat on your way home, activate the alarm system remotely, or check by camera to see whether the cat is back home. There are countless uses for this technology, and solutions are already available for many of these applications, all with their own app, controls, and interface.

LOGO! offers the possibility of covering several applications with one device and one solution. A Web server was integrated into LOGO! 8 that enables self-configured alarm texts to be created in the Web server with the standard software. Function buttons are then used to trigger switching functions, and no HTML knowledge is required. With the latest version of the LOGO! 8 logic module, users can design websites themselves – also with no HTML knowledge required – and create their own background images and self-defined switching elements. Various display resolutions can also be set for the desired end devices, such as smartphones, tablets, and PCs. The LOGO! Web editor is free of charge and available online as a download.



RS Stock No. 165-3222

**Search "LOGO 8" At RS Online today!**



# New Products

## SIRIUS ACT Illuminated Red Push Button

- Illuminated pushbutton, 22 mm, round, plastic, red, pushbutton, flat, momentary contact type, with holder, 1 NC, LED module with integrated LED 230 V AC, screw terminal



**173-6777** Complete Unit NC Momentary 3SU1106-0AB20-1CA0

## LOGO! 8.2 Logic Module with Display

- Integrated Web Server Refined screen giving a new look and feel to the Logic Module
- 6 line display with 16 characters per line meaning more specific messages can be used via text
- Optical emphasis of alarms catered for thanks to the selectable white, orange & red backlighting
- Logic Modules are compatible for all voltage



**165-3222** 24 V dc 6ED1052-1CC08-0BA0  
**165-3226** 12 → 24 V dc 6ED1052-1MD08-0BA0

## Sirius 1 Pole Contactor Relay

- ON delay 1 change-over contact, 1 time range 0.05...1 s 24/230 V AC and 24 V DC with LED, Screw terminal



**171-8299** CO, 3 A 7PV1511-1AP30

## LOGO! 8.2 Starter Kit

- LOGO! starter kit 12/24RCE with LOGO! 12/24RCE, LOGO! SOFT Comfort V 8.2, WinCC Basic, power supply, screwdriver in Systainer



**165-3281** 12 → 24 V dc 6ED10573BA010AA8

## SIMATIC STEP 7 PLC Programming Software

- Easy-to-use engineering system for the SIMATIC S7-1200 PLC and the associated I/O. It is highly efficient and future-orientated and provides an intuitive solution for all your automation tasks



**141-7357** S7-1200 - Programming Software V14 6ES7822-0AA04-0YA5

## 7 Function Time Delay Relay

- Multifunction 2 change-over contacts, 7 functions 7 time ranges 0.05 s
- 100 h 12-240 V AC/DC with LED, Screw terminal



**171-8298** Screw 7PV1508-1BW30

## LOGO! 8.2 TD Text Display

- LOGO! TD Text Display, 6-line, 3 background colors, 2 Ethernet ports, installation accessories for LOGO! 8



**165-3231** 12 → 24 V dc With Display 6ED1055-4MH08-0BA0

## LOGO! 8.2 Logic Module Without Display

- Integrated Web Server Refined screen giving a new look and feel to the Logic Module
- 6 line display with 16 characters per line meaning more specific messages can be used via text
- Optical emphasis of alarms catered for thanks to the selectable white, orange & red backlighting
- Logic Modules are compatible for all voltages



**165-3229** 24 V dc, 8 x Input, 4 x Output 6ED1052-2HB08-0BA0

## ON-Delay Time Delay Relay

- ON delay 1 change-over contact, 1 time range
- 100 s 24 V/110 V AC and 24 V DC with LED, Screw terminal



**171-8300** Screw 7PV1513-1AQ30

### SIRIUS 3RH2 contactor relay

- Climate-proof, finger safe contactor relays. RC elements, varistors, diodes or diode assemblies (combination of a diode and a Zener diode) can be plugged onto all contactor relays for damping opening surges in the coil



**123-9415** 3NO/NC, 10 A, 24 V dc 3RH2131-2BB40

### Suppressor for use with 3RH, 3RT Contactors

- Suppression accessories for Siemens contactors designed to limit the impact of surges and inductive voltage spikes



**392-7908** Diode suit size S00 3RT19161DG00

**392-9645** Varistor suit size S0,S2,S3 3RT19261BB00

### Sentron Non Fused Isolator Emergency Switch

- Main and emergency stop switch
- Handle available in black or red/ yellow (emergency stop)
- Accepts 3 padlocks
- Front panel seal IP65



**518-6783** 25 A, 9.5 kW, IP65 3LD21030TK53

### Sentron Series 7 Digit Analogue Digital Counter

- 48 x 48 mm in size and are for front panel mounting
- Used in control cabinets for control and mechanical engineering purposes
- Used to help plan maintenance intervals, the sentron series are a suitable choice in various applications



**123-9481** 50Hz, 230 V ac 7KT5502

### 3SB3 series Red 22mm Mushroom Head Emergency Buttons

- The Emergency Stop Mushroom Pushbuttons represents worldwide standards
- IP67 where a device can withstand immersion in one meter of water for 30 minutes
- The service life for IEC 60068-2-6 is up to 300000 switching cycles



**453-3100** Twist to Reset 3SB35001HA20

**453-3116** Pull to Reset 3SB35001TA20

### Signum Red 40mm Mushroom Head Emergency Button

- 22mm plastic round complete unit combination, with yellow backing plate screw terminal, 1nc with holder red inscription



**528-0986** Twist to Reset 3SB32031HA20

### Sirius Classic 3RT1 3 Pole Contactors

- Excellent reliability and are of extremely good quality
- Various NO/NC models available
- Maximum switching voltage 690V
- Mechanical life 3 x 10<sup>7</sup> operations



**246-4311** 32 A, 15 kW, 24 V dc Coil 3RT10341BB40

**246-4377** 50 A, 22 Kw, 230 V ac Coil 3RT10361AP00

### Sirius Single Phase Solid State Relay

- Single phase currents up to 50A AC can be switched
- 2 voltage ranges available both with 24Vdc control voltage
- Isolation voltage; 600Vac



**467-4762** -25 → +60°C 3RF23201AA02

### Enclosed Pushbutton Station

- Square enclosure for command and signaling devices with standard equipment
- 32mm Mushroom Head Emergency Stop
- 1 x N/C with screw terminals
- Twist to Reset



**638-7454** Twist to Reset 3SB38010DG3



## Lamp Removal Tool

- For inserting the holder or lamp holder



**612-9911** N/O or N/C contact 3SB29082AA

## 3SB3 Series Black Push Button

- 22mm plastic round complete unit combination: pushbutton with flat button screw terminal, 1nc with holder black



**744-8872** NC Momentary 3SB3203-0AA11

## SIRIUS 3RP15 Multifunction Timer Relay

- Multifunction
- LED for indicating timing relay on voltage
- LED for indicating relay switched
- Function selector switch
- Time setting range selector switch
- 22.5mm wide housing and compact design



**746-5114** 24 V dc, 100 → 127 V ac 3RP1505-1BQ30

## 3SB35 Series 50° Rotary Switch

- Illuminated
- 3 switch positions (I - O - II)
- Momentary contact and/or latching versions
- Standard, heavy duty or with long handle versions
- Protection rating of IP67



**743-0082** 3 Position, Spring Return Actuator 3SB3500-2EA11-0PA0

## 3SB3 Series Green Push Button

- 22mm metal round complete unit combination: pushbutton momentary contact type with flat button screw terminal, 1no with holder green



**745-0360** NO Momentary 3SB3602-0AA41

## 4PDT Non-Latching Relay

- The complete LZS devices consist of a socket, plug-in relay, hold/reject clip, LED module and inscription label
- All designs boast tried and tested screw or push-in, spring loaded terminals with hard gold-plated contacts for optimum interaction with electronic controls
- The PT relay design does not feature a latching mechanism



**758-6891** 24V dc Coil, 6 A LZXP570024

## 3SB35 Series Long handle Selector Switch Head

- Illuminated
- 3 switch positions (I - O - II)
- Momentary contact and/or latching versions
- Standard, heavy duty or with long handle versions
- Protection rating of IP67



**743-0275** 3 Position, Latching 3SB3500-3SA11

## Sirius 3RW40 Series 32 A Soft Starter

- May be integrated into a motor control system using other Sirius control gear products, e.g. 3 pole circuit breakers from the 3RV10 range (see Control Gear section)
- Two phase control, plus soft starting and stopping of three phase asynchronous motors
- Low power loss



**420-508** IP20, 15 kW, 200 → 480 V ac 3RW4027-1BB14

## 3UG Series Monitoring relay

- Single point and two point level monitoring
- Overflow protection
- Dry run protection
- Leak monitoring



**758-6927** 24 → 240 V ac/dc 3UG4501-1AW30

### SITOR Cylindrical Fuses

- Operating class aR (full-range semiconductor protection)
- For protecting high-quality devices and components, such as semiconductor contactors, electronic relays (solid state), converters with fuses in input and in DC intermediate circuit, UPS systems and softstarters for motors of up to 100 A



**395-783** 16A, 10 x 38mm 3NC1016  
**395-806** 25A, 10 x 38mm 3NC1025

### SIRIUS ACT LED Yellow Pilot Light Complete Unit

- Easy installation
- Suitable for use in extreme environments
- No special tools required
- Simple geometry for mounting holes



**874-2061** 22mm Cutout, IP20, 24 V ac/dc 3SU1102-6AA30-1AA0  
**874-2389** Legend Plate 12.5 mm x 27 mm 3SU1900-0AG10-0AA0

### Sirius Black Siren

- Advanced Design
- Improved Illumination
- Thermoplast Enclosure



**124-8921** 24 V dc 8WD4420-OEA

### Sirius Dual Channel Configurable Safety Relay

- Compact design, creates more space in the control cabinet
- Flexible connectivity
- Removeable terminals



**498-949** 4 Safety Contacts and 1 Auxiliary Contact 3TK2826-1BB40

### Sirius Innovation 3RT2 3 Pole Contactor

- Screw connection / Spring Clamp
- Impulse voltage resistance 6 kV
- Insulation voltage 690 V
- Real loss power only 4 W



**875-1040** 50 A, 22 kW, 230 V ac Coil 3RT2036-1AP00

### IoT2020 Educational Intelligent Gateway

- Programming in high-level languages
- Intel Quark x1000 (Galileo)
- 512 MB RAM
- microSD Card slot
- 1 Ethernet Interface



**124-4037** IoT2020 6ES7647-0AA00-0YA2

### SIRIUS ACT Blue Push Button Complete Unit

- Easy installation
- Suitable for use in extreme environments
- No special tools required
- Simple geometry for mounting holes



**874-1932** NO Momentary 3SU1100-0AB50-1BA0

### 3RT Series Control Relay

- Screw Connection
- All models vary with Current rating and Voltage.
- Various NO/NC Values



**122-9435** 3NO, 9 A, 22 A, 24 V dc 3RT2016-1JB41

### IoT2040 Industrial Intelligent Gateway

- Programming in high-level languages
- Intel Quark x1020 (+Secure Boot)
- 1 GB RAM
- microSD Card slot
- 2 Ethernet Interfaces, 2 x RS232/485 interfaces
- Yocto Linux support
- LEDs, battery buffered RTC, watchdog



**124-4038** 1 GB, 8 FLASH MB, 256 kB 6ES7647-0AA00-1YA2







# Need a Quote?

You'll get great savings every time with our Quotation Service.

Contact us to see how much you could save:

**1300 656 636**

[quotesandtenders@rs-components.com](mailto:quotesandtenders@rs-components.com)



[au.rs-online.com](http://au.rs-online.com)

